



taylor&dolman



GL5.2

Mobile lifter

– making transfers easier, reducing the risk of back injuries to care providers, and improving the comfort and safety for both the carer and user.

The GL5.2 mobile lifters are the floor-based alternatives to the ceiling mounted lifting solutions offered in the Guldmann range of products.

The GL5.2 lifter is available as two different models, with the lifting capacity of 155 or 205 kg, respectively. Both models feature electric lifting and width

adjustment to allow easy access around chairs, baths and the ability to lift from the floor.

Lifting to and from the floor

GL5.2 can lift directly from the floor to a chair or bed. This makes a GL5.2 the ideal solution if an unforeseen lifting need occurs where there is no ceiling mounted hoist available.

Lifting to and from the bed

GL5.2 ensures effective lifting to and from the bed. The ability to lift high and

the long reach result in the user can be placed correctly into the middle of the bed, or be positioned correctly into a wheelchair.

Heavy lifting

With the capacity to lift 205 kg the GL5.2 is capable of lifting bariatric patients.

Horizontal lifting

With the advanced design of the lifting height and reach the GL5.2 is well suited for horizontal lifting with the Guldmann stretcher style accessories.

Guldmann™



The characteristics of GL5.2

- Low reach – ability to lift directly from the floor
- High reach – ability to lift tall users in large slings, without difficulty
- Flexible – with the appropriate type of sling / accessories the GL5.2 can deal with all moving and handling requirements
- User friendly – easy for both tall and short people to use.
- Safe – the GL5.2 is strong, stable and reliable – designed for intensive use in professional working environments
- Reliable – the GL5.2 features a visual indicator warning if the lifter is overloaded as well as the battery capacity is indicated in 3 intervals:
 - Low 0 - 25%
 - Medium 25 - 50%
 - High 50 - 100%Audio signal at low battery voltage when approx. 25%.
- Visual service indicator lights up when maintenance is required.
- Strong, noiseless and fast Linak actuators
- Modern design – offering on or off board charging, to suit to environment in which the GL5.2 is used.
- All round capabilities – the GL5.2 makes it easy to deal with a wide range of moving and handling situations while being ergonomically sound and safe for both the care provider and user.

| Time to care |

taylordolman

tel: 0845 838 0600

email: info@taylordolman.com

www.taylordolman.com